




IZT43, Nozzle Type Ionizer, Separate Controller and Power Supply Module IZT43-L36HP-3FU

Datasheet

General series information

- Separate controller nozzle-type ionizer
- IO-Link compatible
- Compact: Height 32 mm x Width 16 mm
- IZTC41 controller can control a maximum of 4 ionizers
- Monitor and operate nozzles which are installed in an inaccessible location
- Multiple alarms & functions
- Static elimination with no air supply.

Standard specifications


Emitter Cartridge Type	L (Energy Saving Static Neutralization Cartridge)
High Voltage Cable Length	3 (3m)
One-touch fitting	6H (ø6 Straight)
Input/Output	P (PNP)
Power Supply Cable Length	3 (3m)
Communication Cable Entry Direction/Length	None
Nozzle Bracket	F (Angle Adjustment Bracket)
DIN Rail Mounting Bracket	U (Controller: Included; Supply Module: Included)
Pressure medium	Air (Clean, dry air)
Maximum operating pressure	0.7 MPa
Maximum ambient temperature	40 °C
Minimum ambient temperature	0 °C
General power supply	24 VDC ±10 %
Conform to the European RoHS Directive	Conform
Approvals	CE, UKCA
Current consumption	0.4 A or less


Specifications are subject to change without prior notice and any obligation on the part of the manufacturer.

Material	Cover: ABS, Aluminium. Switch: Silicone rubber
Ion generation method	Corona discharge
Method of applying voltage	AC, DC
Applied voltage	±6000 V
Ambient humidity	35 to 65% RH (No condensation)
Offset voltage	±30 V or less
Effective static neutralization distance	50 to 2000 mm
Technical graph 1	165701_graph1B_en.jpg
Graph1 title	Installation distance and discharge time

Technical information graphs



Installation distance and discharge time





Constructions

IZT43(-L) series



No.	Description
1	Controller
2	High voltage power supply module
3	Nozzle
4	Emitter cartridge
5	High voltage cable
6	One-touch fitting
7	Bracket
8	Power supply cable
9	Communication cable

Additional information

Catalogue	IZT40-41-42-43-D_EU.pdf
Declaration of conformity	newDoC_Izt_TF122006EN.pdf newDoC_Izx_TFV0004EN.pdf
Installation manuals	IM_Izt_TF2Z267EN.pdf
Operation manuals	OM_Izt-L_OMZ0045EN-A.pdf OM_Izt41-42-L_OMT0049EN-E.pdf